

Technical product specification 2013.04.19 PP


CHROMATECH ultra Spacer bar: Version F





ROLLTECH A/S - an Alu-Pro Group Company

1. Spacer properties



1.1 Cross section and tolerances

| Spacer bar / cavity | Н | H(c) | Butyl | В | B1 | Х | Volume | *T |
|---------------------|----------|------|---------|----------|-------------|---------|-----------|----------|
| | | | area | | | | Desiccant | Standard |
| | +/- 0.15 | | +/- 0.1 | +/- 0.15 | -0.05/+0.25 | +/- 0.1 | Grace 551 | steel |
| | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | g/m | [mm] |
| CHROMATECH ultra 8 | 6.9 | 6.3 | 4.82 | 7,6 | 7.5 | 2,45 | 20,2 | 0,10 |
| CHROMATECH ultra 10 | 6.9 | 6.3 | 4.82 | 9.6 | 9.5 | 4.45 | 32,5 | 0.10 |
| CHROMATECH ultra 12 | 6.9 | 6.3 | 4.82 | 11.6 | 11.5 | 6.45 | 36,3 | 0.10 |
| CHROMATECH ultra 13 | 6.9 | 6.3 | 4.82 | 12.6 | 12.5 | 7.45 | 40,5 | 0.10 |
| CHROMATECH ultra 14 | 6.9 | 6.3 | 4.82 | 13.6 | 13.5 | 8.45 | 44,7 | 0.10 |
| CHROMATECH ultra 15 | 6.9 | 6.3 | 4.82 | 14.6 | 14.5 | 9.45 | 48,6 | 0.10 |
| CHROMATECH ultra 16 | 6.9 | 6.3 | 4.82 | 15.6 | 15.5 | 10.45 | 52,4 | 0.10 |
| CHROMATECH ultra 18 | 6.9 | 6.3 | 4.82 | 17.6 | 17.5 | 12.45 | 60,2 | 0.10 |
| CHROMATECH ultra 20 | 6.9 | 6.3 | 4.82 | 19.6 | 19.5 | 14.45 | 67,9 | 0.10 |
| CHROMATECH ultra 22 | 6.9 | 6.3 | 4.82 | 21.6 | 21.5 | 16.45 | 76,1 | 0.10 |
| CHROMATECH ultra 24 | 6.9 | 6.3 | 4.82 | 23,6 | 23.5 | 18,45 | 84,0 | 0,10 |

*T: Standard is 0.10 mm for the F version. The spacer can be supplied with a special steel thickness. A number after the F will then indicate the thickness. Example: F8 means the steel is 0.08 mm in thickness.

| Ref. No. | EN Ref. | Description/specification | Internal test method | |
|---------------------------|------------|--|----------------------------------|--|
| Further Spacer properties | | | | |
| 1.2 | 2.3 2.4 | Geometry/shape The spacer geometry is shown in the cross section picture above. On enquiry a specific drawing can be delivered. Tolerances above. | Slide gauge and inspection drift | |
| 1.3 | 2.2 | Length and straightness Standard length is 6,000 mm +/- 10 mm. Straightness deviation 15 mm/m at room temperature. | Steel ruler. Visual. | |
| | | /S, DK-9800 Hjörring. matech ultra (F) | Page 1 of 3 | |



Technical product specification 2013.04.19 PP

CHROMATECH ultra





ROLLTECH A/S - an Alu-Pro Group Company

| 1.4 | 2.7 | Undesired openings | |
|-------|--------|---|-------------------------|
| | | The spacer is tight as the backside is one uninterrupted piece of material. | Process validation. |
| | | Plastic and steel are glued together with a PU hotmelt. | |
| 1.5 | 2.6 | Perforation. Se comments below ** | |
| | | Calibrated perforation holes measured for optimal performance. | Air flow meter. |
| 2.0 5 | Spacer | r material | |
| 2.1 | | Material for calculations | |
| | | Steel material used is according to DIN EN 10 088 type 1.4372 (AISI 201) | Documented by |
| | | or similar grades. Thermal conductance $\lambda_s = 15$ W/mK at 20 °C. | supplier. |
| | | Engineered plastic based on PVC λ_p = 0.17 W/mK acc. EN ISO 10077-2. | |
| | | These values are to be used for calculations. DXF file can be supplied. | |
| ~ ~ | 0.5 | Total box model height: H(c) + sealant = 6,3 mm + 3 mm = 9,3 mm. | |
| 2.2 | 2.5 | Surface | Visual test & |
| | | The surface is clean and do not undergo any treatment with chemicals. RAL colours 9004, 7035, 7040, 8003, 8016 and 9016. | Adhesion test. |
| | | RAE colours 9004, 7033, 7040, 8003, 8010 and 9010. | Autresion test. |
| 2.3 | | Tolerances of the steel material | |
| | | The wall thickness of the spacer "F" is standard 0.10 mm. | Micrometer. |
| | | Other thicknesses are available on request. | |
| 2.4 | | Lubrication | |
| | | During the forming of the spacer lubrication is used. The lubrication will | Adhesion test. |
| | | evaporate fully leaving no volatile elements. | |
| 2.5 | 2.8 | Volatile elements | |
| | | Volatile elements are tested according to EN 1279-6 annex G. | Weight loss test. |
| | | | M _v measured |

** 1.5.1 Level of perforation

The Rolltech standard perforation will reduce the absorption of aqueous vapour to be app. 1.0 weight % over a period of 24 hours (16 mm cavity tested by Grace Davidson Europe) - relative to the spacer size. The perforation is targeted EN 1279 - 6 annex A – specified maximum preload $H_20 \le 3$ %.

** 1.5.2 Function of the perforation

The perforation holes are until a certain particle size able to detain dust from the desiccant. This point is particular related to the performance of the bending machine and to the desiccant quality. An incorrect adjustment of the bending tool can cause damage to the perforation.

3.0 Quality aspects

3.1 Quality management

ROLLTECH A/S is certified according to DS EN ISO 9001.

3.2 Tests of the product

Processes and routines are established to secure the quality of the delivered material. During production the spacers are continuously monitored through systematic and random checks. Data will be available for a period of 5 years.

3.3 Quality agreement

ROLLTECH A/S fulfil the requirements of EN 1279 - 6 annex A. Specific quality agreement can be made to reduce inspection and test of the incoming material according to EN1279-6 part 5.2.6.

| ROLLTECH A/S, DK-9800 Hjörring. | |
|---------------------------------|-------------|
| DB UK - Chromatech ultra (F) | Page 2 of 3 |



Technical product specification 2013.04.19 PP

CHROMATECH ultra Spacer bar: Version F





4.0 Customer focus and warranty

On all spacers ROLLTECH offers a 5 year product warranty. The warranty covers free exchange of spacers in case of a defect. The spacers must have been stored, installed and used according to present norms and technical standards. Special solutions and **usage** that **are not standardized** will need prior approval in writing from ROLLTECH in order to be covered. Related to temperature standardized condition for IG is -30° to 70°C.

4.1 Storage and use

To secure the performance of the spacers, the stock conditions must be acceptable. Broken packaging, humidity and variation in temperature will have an effect on the spacer in general. Make sure the spacer is conditioned at room temperature before use.

Preferred conditions will be a room temperature over 15°C and humidity RH of minimum 45% Avoid having an environment with a high concentration of dust.

General handling and attention according to safety data sheet for the spacer. Use gloves when handling the spacer/frames and make sure there is exhausting when cutting the spacer.

It is recommended to check out and control all the specific points above.

4.2 Adhesion check

When preparing samples for adhesion test according to EN1279-6 F3.2.2 make sure the spacer backside is covered and in full contact with the sealant (no air bubbles). When pulling the samples make sure to support the spacer fully inside to avoid deformation. If the spacer deforms the adhesion test will be affected.

4.3 Pressure

Deformation by pressure such as wind load and weight load by horizontal installation.

Compression data for a 16 mm CU cavity:

50 N/cm \rightarrow 0 mm; 80 N/cm \rightarrow 0.3 mm; 110 N/cm \rightarrow 0.5 mm.

4.4 System performance

It is always necessary to check if the system consisting of spacer, bending machine and corresponding corner quality, connector/corner and desiccant works well together. Important to check is also compatibility of the whole system.

4.5. Cleaning the plastic surface

If for some reason the plastic surface is defiled by dust from other materials it can be cleaned again by the use of water or air. Dust can easily be removed with antistatic loaded compressed air or a moist cloth.

The surface is particularly sensitive to esters, ketones and PAH. Check reaction before use!

4.6 UV stability

The plastic used is an organic material with UV stabilizer in order to minimize the ageing effect caused by sun light.

The material is tested for 3.000 hours according to EN ISO 4892-1 & En 4892-2 method A, cycle 1. Evaluation is done according to grey scale index.